PRODUCT INFORMATION

# DURATECH

## TOP125x50-Ø25 TFR

EAN 4031582478792



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●● |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●● |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Duratech |
| Type | Wheel |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 700 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 1400 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 0.81 kg |

### WHEEL

| | |
|---|---|
| Body material | Polyamide, heavy |
| Tread Material Mix | Identical with wheel body |
| Bearing | Precision ball bearing |
| Threadguards | Without threadguard |
| Diameter | 125 mm |
| Tread width | 50 mm |
| Axle Hole Diameter | 25 mm |
| Hub Length | 60 mm |
| Hardness of tread (D) | 75 Shore D |
| Bearing type | 6204 |

© Copyright 2026 TENTE International GmbH