PRODUCT INFORMATION

SUPRATECH

PJO3.5x1.25-Ø0.5 HL40

EAN 4031582436051



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 1.8 mph	209.44 lb
Electric conductive	no
Stainless	no
Load capacity Static	418.88 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	3.5 in
Tread width	1.25 in
Axle hole diameter	0.48 in
Hub length	1.57 in
Hardness of tread (A)	77 Shore A

© Copyright 2026 TENTE International GmbH


SUPRATECH

PJO3.5x1.25-Ø0.5 HL40

EAN 4031582436051

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH