PRODUCT INFORMATION

DURATECH

TOP 082x98-Ø20 HL100

EAN 4031582322668



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread Material Mix	Identical with wheel body
Bearing	Precision ball bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	82 mm
Tread width	98 mm
Axle Hole Diameter	20 mm
Hub Length	100 mm
Body width	98 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

PERFORMANCE

Roll Performance	●●●●●
Movement Noise	●●○○○
Attrition	●●●●●
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	900 kg
Load capacity at 6 km/h	720 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1800 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.58 kg

© Copyright 2026 TENTE International GmbH

DURATECH

TOP 082x98-Ø20 HL100

EAN 4031582322668

Order number 00804410

Product Drawings





