PRODUCT INFORMATION

STYLEA

5925UAP100L51-11 DOM41

EAN 4031582370652



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel caster with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	3.98 in
Overall width	2.95 in

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	4.41 in
Swivel interference	8.82 in
Dome diameter	1.61 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Axle	Riveted
Threadguards	With threadguard
Diameter	3.94 in
Tread width	0.79 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.43 in

© Copyright 2026 TENTE International GmbH


STYLEA

5925UAP100L51-11 DOM41

EAN 4031582370652

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH