

LUMINA

A525POI050P41 TFR

EAN 4031582395327



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	56 mm
Overall width	54 mm
Overall weight	0.056 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	7 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Swivel radius	62 mm
Swivel interference	124 mm

FITTING

Fitting type	Square plate
Plate length	38 mm
Plate width	38 mm