

OMIKRON TWIN

9958FCP200P65

EAN 4031582492460



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Omikron twin
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2000 kg
Load capacity at 6 km/h	1600 kg
Load capacity Static	4000 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	60 °C
Overall height	275 mm
Overall width	154 mm
Overall weight	15.768 kg

WHEEL

Body material	Cast iron
Tread material	Ultratech Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Hardness of tread (D)	42 Shore D

HOUSING

Material fork	Iron forged, heavy
Fork shape	Twin wheel housing
Dome diameter	160 mm

FITTING

Fitting type	Rectangular plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	160 mm
Plate hole width (Maximum)	120 mm
Plate hole diameter	15 mm

OMIKRON TWIN

9958FCP200P65

EAN 4031582492460



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

