

NOVATECH

FTP 200x80-Ø25 HL92

EAN 4031582319354



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL


Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	7.87 in
Tread width	3.15 in
Axle hole diameter	0.98 in
Hub length	3.62 in
Body width	3.15 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	3703.76 lb
Load capacity at 3.7 mph	3086.47 lb
Electric conductive	no
Stainless	no
Load capacity Static	6172.94 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	15.53 lb




PRODUCT INFORMATION

NOVATECH

FTP 200x80-Ø25 H192

EAN 4031582319334



BETTER MOBILITY. BETTER LIFE.