

# AGILA US

2670PAP3X1.25P30-13



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila US
Housing type	Swivel castor
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 1.8 mph	224.87 lb
Load capacity Static	449.74 lb
Overall height	3.98 in

## WHEEL

Body material	Polypropylene
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3 in
Tread width	1.25 in
Axle hole diameter	0.39 in
Hub length	1.61 in
Hardness of tread (D)	41 Shore D

## HOUSING

Material	Steel sheet, medium
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Offset	1.42 in
Swivel radius	2.89 in
Swivel interference	5.83 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in