

# STYLEA

5925PJI040L51-10 LOW RAL9011

EAN 4031582441994



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	43 mm
Overall width	52 mm
Overall weight	0.054 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	40 mm
Tread width	12 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	12 mm
Swivel radius	45 mm
Swivel interference	90 mm
Dome diameter	15.2 mm

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm

# STYLEA

5925PJI040L51-10 LOW RAL9011

EAN 4031582441994



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

