

# STYLEA

5920UOI065B10-11X20 DOM32

EAN 4031582310870  
Order number 00078717



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor
Load capacity at 3 km/h	50 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	72 mm
Overall width	46 mm
Overall weight	0.124 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	65 mm
Tread width	7 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	53 mm
Swivel interference	106 mm
Dome diameter	32 mm

## FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm

PRODUCT INFORMATION

# STYLEA

5920UOI065B10-11X20 DOM32

EAN 4031582310870  
Order number 00078717



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

