

ALPHA

3470BOG100P30-13

EAN 4031582413410



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Alpha
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	125 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	250 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall Height	128 mm
Overall weight	0.69 kg

HOUSING

Housing Material	Steel sheet, heavy
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	40 mm
Swivel radius	90 mm
Swivel interference	180 mm

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread Material Mix	Identical with wheel body
Bearing	Dry bearing bush
Axle	Screwed with nut
Diameter	100 mm
Tread width	35 mm
Hardness of tread (D)	90 Shore D

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ALPHA

3470BOG100P30-13

EAN 4031582413410



BETTER MOBILITY. BETTER LIFE.

Product Drawings

3470...100P30-13

