

# AGILA STAINLESS

7470PJC125P50

EAN 4031582349986



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○   |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila stainless           |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 100 kg                    |
| Electric Conductive         | No                        |
| Stainless                   | Yes                       |
| Load capacity Static        | 200 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall Height              | 160 mm                    |
| Overall width               | 60 mm                     |
| Overall weight              | 0.72 kg                   |

## HOUSING

|                     |                         |
|---------------------|-------------------------|
| Housing Material    | Stainless steel, medium |
| Fork shape          | Broad                   |
| Swivel Bearing      | Two ball races          |
| Housing Color       | Stainless steel         |
| Offset              | 41 mm                   |
| Swivel radius       | 103.5 mm                |
| Swivel interference | 207 mm                  |
| Dome diameter       | 60 mm                   |

## WHEEL

|                       |                                   |
|-----------------------|-----------------------------------|
| Body material         | Polypropylene                     |
| Tread Material Mix    | Thermoplastic rubber              |
| Bearing               | Precision ball bearing, stainless |
| Wheel Color           | Silver grey (RAL7001)             |
| Threadguards          | With threadguard                  |
| Diameter              | 125 mm                            |
| Tread width           | 32 mm                             |
| Body width            | 32 mm                             |
| Hardness of tread (A) | 87 Shore A                        |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 77 mm             |
| Plate width                 | 67 mm             |
| Plate hole length (Minimum) | 46.5 mm           |
| Plate hole length (Maximum) | 51.5 mm           |
| Plate hole width (Minimum)  | 56 mm             |
| Plate hole width (Maximum)  | 61.5 mm           |
| Plate hole diameter         | 8.5 mm            |

# AGILA STAINLESS

7470PJC125P50

EAN 4031582349986

Order number 00036342  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

