

# ALPHA STAINLESS

8470BOG100P30-11 HT

EAN 4031582378184  
Order number 00061131



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	●●●○○
Movement noise	●●○○○○
Attrition	●●●●●
Corrosion resistance	●●●●●

## CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	125 kg
Stainless	✓
Load capacity Static	250 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	250 °C
Overall height	128 mm
Overall width	75 mm
Overall weight	0.682 kg

## WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Axle	Screwed with nut
Wheel color	Black
Diameter	100 mm
Tread width	35 mm
Body width	35 mm
Hardness of tread (D)	90 Shore D

## HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	41 mm
Swivel radius	91 mm
Swivel interference	182 mm
Dome diameter	75 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

# ALPHA STAINLESS

8470BOG100P30-11 HT

EAN 4031582378184  
Order number 00061131



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

8470U0D100P30- $\phi$ 11

