

AGILA

2478YGO050P41

EAN 4031582356397



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila |
| Type | Fixed castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 110.23 lb |
| Electric conductive | ✓ |
| Load capacity Static | 220.46 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 2.72 in |
| Overall weight | 0.23 lb |

WHEEL

| | |
|-----------------------|---|
| Body material | Polypropylene, electric conductive |
| Tread material | Thermoplastic rubber, electric-conductive |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 1.97 in |
| Tread width | 0.75 in |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 2.17 in |
| Plate width | 2.17 in |
| Plate hole length (Minimum) | 1.52 in |
| Plate hole length (Maximum) | 1.73 in |
| Plate hole width (Minimum) | 1.52 in |
| Plate hole width (Maximum) | 1.73 in |
| Plate hole diameter | 0.25 in |

AGILA

2478YGO050P41

EAN 4031582356397



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

