

AGILA CARE

2476XSP125R26-28S45 D

EAN 4031582358063
Order number 00034559



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--|
| Product name | Agila care |
| Type | Swivel castor with central, total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric conductive | ✓ |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 163 mm |
| Overall width | 67 mm |
| Overall weight | 1.017 kg |

WHEEL

| | |
|-----------------------|---|
| Body material | Polyamide, electric conductive |
| Tread material | Polyurethane, injected, electric-conductive |
| Bearing | Precision ball bearing |
| Wheel color | Silver grey (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 125 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 91 Shore A |
| Hardness of tread (D) | 40 Shore D |

HOUSING

| | |
|---------------------|---------------------|
| Material fork | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Colour | Blue passivated |
| Offset | 41 mm |
| Swivel radius | 103.5 mm |
| Swivel interference | 207 mm |
| Dome diameter | 67 mm |

FITTING

| | |
|------------------------------|-------------------------------------|
| Brake cam | hex cam |
| Fitting type | Stem with cam hole for profile bars |
| Bolt diameter | 28 mm |
| Bolt length | 96 mm |
| Bolt thread position | 19 mm |
| Bolt mounting holes quantity | 2 |

AGILA CARE

2476XSP125R26-28S45 D

EAN 4031582358063
Order number 00034559



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

