

AGILA

2478DYK050P41-55

EAN 4031582344479
Order number 00028596



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Fixed castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Electric conductive	✓
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	69 mm
Overall width	35 mm
Overall weight	0.154 kg

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black, electric-conductive
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Colour	Blue passivated
Dome diameter	27 mm

FITTING

Fitting type	Square plate
Plate length	55 mm
Plate width	55 mm
Plate hole length (Minimum)	38.5 mm
Plate hole length (Maximum)	44 mm
Plate hole width (Minimum)	38.5 mm
Plate hole width (Maximum)	44 mm
Plate hole diameter	6.3 mm

AGILA

2478DYK050P41-55

EAN 4031582344479
Order number 00028596



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

