

LEVINA LIGHT

5225PJP075L51-10

EAN 4031582477061



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Levina light
Type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	165.35 lb
Load capacity Static	330.69 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	4.06 in
Overall weight	0.39 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polyamide
Fork shape	Straight
Swivel bearing	Stem, swiveling
Offset	1.06 in
Swivel radius	2.87 in
Swivel interference	5.75 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

LEVINA LIGHT

5225PJP075L51-10

EAN 4031582477061



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

