

KAPPA

9680FTP200P63 WT50

EAN 4031582452945



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa
Housing type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1200 kg
Load capacity at 6 km/h	1000 kg
Load capacity Static	2400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	245 mm
Overall weight	7.083 kg

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	59 mm
Swivel radius	159 mm
Swivel interference	318 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

TECHNICAL DRAWINGS

