

AGILA

2470UAP050P30-11

EAN 4031582324631
Order number 00031410



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	69 mm
Overall width	43 mm
Overall weight	0.165 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	50 mm
Tread width	20 mm
Body width	20 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	24 mm
Swivel radius	49 mm
Swivel interference	98 mm
Dome diameter	41 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm
Hint	Castors can be mounted with standard screws of any length.

AGILA

2470UAP050P30-11

EAN 4031582324631
Order number 00031410



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

