

ALPHA STAINLESS

8477BOG100P62

EAN 4031582432985



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel caster with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	275.58 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	551.16 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall height	5.04 in
Overall weight	1.59 lb

HOUSING

Housing Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Stainless steel
Offset	1.61 in
Swivel radius	3.58 in
Swivel interference	7.17 in

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Axle	Screwed with nut
Diameter	3.94 in
Tread width	1.38 in
Hardness of tread (D)	85 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	4.13 in
Plate width	3.35 in
Plate hole length (Minimum)	3.03 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Maximum)	2.36 in
Plate hole diameter	0.35 in

ALPHA STAINLESS

8477BOG100P62

EAN 4031582432985



BETTER MOBILITY. BETTER LIFE.

Product Drawings

