

# AGILA TWIN

2975PJH050P30-10,3

EAN 4031582439496



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product Name                | Agila twin                     |
| Type                        | Swivel castor with wheel brake |
| Standard                    | EN12530 - Devices Castors      |
| Load capacity at 3 km/h     | 70 kg                          |
| Electric Conductive         | No                             |
| Stainless                   | No                             |
| Load capacity Static        | 140 kg                         |
| Temperature range (Minimum) | -20 °C                         |
| Temperature range (Maximum) | 85 °C                          |
| Overall Height              | 69 mm                          |
| Overall weight              | 0.36 kg                        |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Twin wheel housing  |
| Swivel Bearing      | Two ball races      |
| Offset              | 25 mm               |
| Swivel radius       | 77 mm               |
| Swivel interference | 155 mm              |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread Material Mix    | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | With threadguard     |
| Diameter              | 50 mm                |
| Tread width           | 19 mm                |
| Hardness of tread (A) | 87 Shore A           |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 11 mm     |

# AGILA TWIN

2975PJH050P30-10,3

EAN 4031582439496



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

