

LEVINA STAINLESS

5381UAC150P30-11

EAN 4031582364279



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Levina stainless
Type	Swivel castor with directional lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	200 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	190 mm

HOUSING

Housing Material	Polyamide
Fork shape	Slim
Swivel Bearing	Two ball races, reinforced or stainless
Offset	38 mm
Swivel interference	240 mm

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	150 mm
Tread width	32 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	40 Shore D

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm



Universal
Design
Award



Deutscher
Designer
Club

LEVINA STAINLESS

5381UAC150P30-11

EAN 4031582364279



BETTER MOBILITY. BETTER LIFE.

Product Drawings



Universal
Design
Award



Deutscher
Designer
Club