

MAXTECH

PNP300x42-Ø12 HL45

EAN 4031582411089



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C

WHEEL

Tread hardness	soft
Body material	Polypropylene
Tread Material Mix	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	300 mm
Tread width	42 mm
Axle Hole Diameter	12 mm
Hub Length	45 mm
Hardness of tread (A)	70 Shore A

