

AGILA

2478YGO050P41

EAN 4031582356397



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Fixed caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	110.23 lb
Electric conductive	Yes
Stainless	no
Load capacity Static	220.46 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.72 in
Overall weight	0.23 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.75 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Square plate
Plate length	2.17 in
Plate width	2.17 in
Plate hole length (Minimum)	1.52 in
Plate hole length (Maximum)	1.73 in
Plate hole width (Minimum)	1.52 in
Plate hole width (Maximum)	1.73 in
Plate hole diameter	0.25 in

AGILA

2478YGO050P41

EAN 4031582356397



BETTER MOBILITY. BETTER LIFE.

Product Drawings

