

LINEA

594CUAP150R05-22

EAN 4031582409055



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Linea
Type	Swivel castor with combined lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	175 mm
Overall width	89 mm
Overall weight	1.45 kg
Certification	Tested and monitored by TÜV Süd

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	150 mm
Tread width	22 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	52 mm
Swivel radius	156 mm
Swivel interference	312 mm
Dome diameter	56 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	22 mm
Bolt length	40 mm



Deutscher Designer Club



Interzum Award



IF Design Award