

# LINEA LIGHT

5925XSI050L51-10

EAN 4031582474756



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Electric conductive	✓
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	50.5 mm
Overall width	47.6 mm
Overall weight	0.073 kg

## WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Tread width	13 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	15 mm
Swivel radius	52 mm
Swivel interference	104 mm
Dome diameter	23 mm

## FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm



Deutscher Designer Club



Interzum Award



IF Design Award

# LINEA LIGHT

5925XSI050L51-10

EAN 4031582474756

## TECHNICAL DRAWINGS

