

PRODUCT INFORMATION

NOVATECH

ETX082x70-Ø17 HL75-B

EAN 4031582331936



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing, sealed
Threadguards	With threadguard
Diameter	82 mm
Tread width	70 mm
Axle Hole Diameter	17 mm
Hub Length	75 mm
Hardness of tread (A)	92 Shore A
Bearing type	6303
Sealing type	B
Suitable for	jungheinrich_mic

PERFORMANCE

Roll Performance	● ● ● ● ○ ○
Movement Noise	● ● ● ● ○ ○
Attrition	● ● ● ● ● ○
Corrosion Resistance	● ● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Load capacity at 3 km/h	700 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	1 kg

