

STYLEA

5925UJI065P41-38X38/10

EAN 4031582410068



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Stylea |
| Housing type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 50 kg |
| Load capacity Static | 100 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 78 mm |
| Overall width | 42 mm |
| Overall weight | 0.107 kg |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 65 mm |
| Tread width | 7 mm |
| Hardness of tread (A) | 87 Shore A |

HOUSING

| | |
|---------------------|--------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 77 mm |
| Swivel interference | 154 mm |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 38 mm |
| Plate width | 38 mm |
| Plate hole length (Maximum) | 27 mm |
| Plate hole width (Maximum) | 27 mm |
| Plate hole diameter | 5 mm |

PRODUCT INFORMATION

STYLEA

5925UJI065P41-38X38/10

EAN 4031582410068



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

