

# AGILA CARE

2476YGO100R36-32S30 4XM6

EAN 4031582342260



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila care
Housing type	Swivel castor with central, total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Electric conductive	✓
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	138 mm
Overall weight	0.838 kg

## WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	38 mm
Swivel radius	88 mm
Swivel interference	176 mm

## FITTING

Fitting type	Stem with cam hole for profile bars, short version
Bolt diameter	32 mm
Bolt length	51 mm

# AGILA CARE

2476YGO100R36-32S30 4XM6

EAN 4031582342260



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

