

# ICS

5320PJP100S70-10X17 7001

EAN 4031582010688



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	ICS
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	5.39 in
Overall width	2.05 in
Overall weight	0.83 lb

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Integrated threadguard
Diameter	3.94 in
Tread width	1.26 in
Body width	1.26 in
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Polyamide
Fork shape	Slim
Swivel bearing	Stem, swiveling
Color	Silver gray (RAL7001)
Offset	1.5 in
Swivel radius	3.43 in
Swivel interference	6.85 in
Dome diameter	2.05 in
Thread diameter	0 in

## FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.67 in



IF  
Design  
Award

## TECHNICAL DRAWINGS

