

# KAPPA FLEX

9750ITP160P63 SH80

EAN 4031582414288



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Kappa flex
Type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	450 kg
Load capacity at 6 km/h	300 kg
Load capacity Static	900 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	220 mm
Overall weight	4.97 kg

## WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Hardness of tread (A)	80 Shore A

## HOUSING

Material fork	Iron forged, heavy
Fork shape	With spring
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	69 mm
Swivel radius	149 mm
Swivel interference	298 mm

## FITTING

Fitting type	Medium rectangular plate
Plate length	142 mm
Plate width	111 mm
Plate hole length (Minimum)	99 mm
Plate hole length (Maximum)	112 mm
Plate hole width (Minimum)	74 mm
Plate hole width (Maximum)	83 mm
Plate hole diameter	12.7 mm