

LINEA SAFETY

592DUAI075L51-10 RAL9002

EAN 4031582378214



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Linea safety
Housing type	Automatic locking system
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	75.5 mm
Overall width	55 mm
Overall weight	0.159 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	75 mm
Tread width	15 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	23 mm
Swivel radius	66 mm
Swivel interference	132 mm
Hint	Force to release 23 N and spring stroke length 8 mm.

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm



LINEA SAFETY


592DUAI075L51-10 RAL9002

EAN 4031582378214



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award