

OMIKRON TWIN

9950FTP125P65

EAN 4031582316759

Order number 00802882

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Omikron twin
Type	Swivel castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 4 km/h	1500 kg
Load capacity at 6 km/h	1100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	3000 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall Height	220 mm
Overall width	189 mm
Overall weight	16.98 kg



BETTER MOBILITY. BETTER LIFE.

HOUSING

Housing Material	Iron forged, heavy
Fork shape	Twin wheel housing
Swivel Bearing	Deep-groove ball thrust roller bearing
Housing Color	Transparent coating
Offset	50 mm
Swivel radius	125 mm
Swivel interference	250 mm
Lubrication nipple	1
Dome diameter	160 mm

WHEEL

Body material	Cast iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	125 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Medium rectangular heavy-duty plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	160 mm
Plate hole diameter	15 mm

OMIKRON TWIN

9950FTP125P65

EAN 4031582316759

Order number 00802882
Product Drawings



BETTER MOBILITY. BETTER LIFE.

