

OMIKRON TWIN

9951FTP400P41-400 TFR

EAN 4031582480764



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Omikron twin
Housing type	Swivel castor with directional lock
Load capacity at 3 km/h	11000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	570 mm
Overall weight	246.984 kg

WHEEL

Body material	Cast iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	400 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	90 mm
Swivel radius	170 mm
Swivel interference	340 mm

FITTING

Fitting type	Square plate
Plate length	400 mm
Plate width	400 mm
Plate hole length (Maximum)	340 mm
Plate hole width (Maximum)	340 mm
Plate hole diameter	22 mm

OMIKRON TWIN

9951FTP400P41-400 TFR

EAN 4031582480764



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

