

AGILA STAINLESS

7475PJO050P30-11

EAN 4031582350937



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Agila stainless
Type	Swivel caster with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.72 in
Overall width	1.69 in
Overall weight	0.37 lb

HOUSING

Housing Material	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Stainless steel
Offset	0.94 in
Swivel radius	2.76 in
Swivel interference	5.51 in
Material brake pedal	polyamide
Dome diameter	1.61 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.75 in
Body width	0.75 in
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in
Hint	Castors can be mounted with standard screws of any length.

AGILA STAINLESS

7475PJO050P30-11

EAN 4031582350937

Order number 00036674
Product Drawings



BETTER MOBILITY. BETTER LIFE.

