

AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



Image may differ from the original product

CORE ATTRIBUTES

Product name	Agila twin
Type	Swivel caster with total lock
Load capacity at 1.8 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Overall height	3.9 in



BETTER MOBILITY. BETTER LIFE.

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	1.22 in
Swivel interference	7.8 in

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.39 in

AGILA TWIN

2977POO75P30-10,3

EAN 4031582428247



BETTER MOBILITY. BETTER LIFE.

Product Drawings

