

# LINEA LOAD

5945UAP050L51-8 LOAD 9011

EAN 4031582421620



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Linea load                     |
| Housing type                | Swivel castor with wheel brake |
| Standard                    | EN12530 - Devices Castors      |
| Load capacity at 1.8 mph    | 220.46 lb                      |
| Load capacity Static        | 440.92 lb                      |
| Temperature range (Minimum) | 14 °F                          |
| Temperature range (Maximum) | 104 °F                         |
| Overall height              | 1.97 in                        |
| Overall width               | 1.87 in                        |
| Overall weight              | 0.2 lb                         |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread material        | Polyurethane, injected |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 1.97 in                |
| Tread width           | 0.51 in                |
| Hardness of tread (A) | 92 Shore A             |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material            | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel bearing      | Precision ball bearing |
| Swivel radius       | 2.01 in                |
| Swivel interference | 4.02 in                |
| Dome diameter       | 0.91 in                |

## FITTING

|                    |                            |
|--------------------|----------------------------|
| Fitting type       | Blind hole for B10 fitting |
| Bolt hole diameter | 0.31 in                    |



# LINEA LOAD



5945UAP050L51-8 LOAD 9011

EAN 4031582421620



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award