

# AGILA TWIN

2977PJH075P30-10,3

EAN 4031582439502



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	99 mm
Overall width	71 mm
Overall weight	0.868 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	31.3 mm
Swivel radius	99 mm
Swivel interference	198 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	10.3 mm

# AGILA TWIN

2977PJH075P30-10,3

EAN 4031582439502



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

