

AGILA

2477DYK075P40

EAN 4031582340532



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Agila
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	55 kg
Electric Conductive	Yes
Stainless	No
Load capacity Static	110 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall Height	100 mm
Overall width	43 mm
Overall weight	0.43 kg

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel Bearing	Two ball races
Housing Color	Blue passivated
Offset	24 mm
Swivel radius	80 mm
Swivel interference	160 mm
Dome diameter	43 mm

WHEEL

Body material	Sheet Steel
Tread Material Mix	Solid rubber, black, electric-conductive
Bearing	Cone ball bearing
Wheel Color	Blue passivated
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Square plate
Plate length	60 mm
Plate width	60 mm
Plate hole length (Minimum)	38 mm
Plate hole length (Maximum)	48 mm
Plate hole width (Minimum)	38 mm
Plate hole width (Maximum)	48 mm
Plate hole diameter	6.3 mm

AGILA

2477DYK075P40

EAN 4031582340532

Order number 00004972

Product Drawings



BETTER MOBILITY. BETTER LIFE.

