

STYLEA

5920UOI035L51-9 LH 9011/9011

EAN 4031582338447
Order number 00074911



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	33 mm
Overall width	52 mm
Overall weight	0.047 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	35 mm
Tread width	12 mm
Body width	12 mm

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Colour	Graphite black (RAL9011)
Offset	12 mm
Swivel radius	37 mm
Swivel interference	74 mm
Dome diameter	15.2 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	9 mm

STYLEA

5920UOI035L51-9 LH 9011/9011

EAN 4031582338447
Order number 00074911



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

