

LINEA LIGHT

5921UAO075S70-M10X15 HN EN12528

EAN 4031582415209



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll performance ●●●●○

Movement noise ●●●○○

Attrition ●●●○○

Corrosion resistance ●●●●○

CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor with directional lock
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.39 in
Overall width	2.17 in
Overall weight	0.47 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.59 in

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	0.91 in
Swivel radius	3.23 in
Swivel interference	6.46 in
Thread diameter	0 in

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.59 in



PRODUCT INFORMATION

LINEA LIGHT

5921UAO075S70-M10X15 HN EN12528

EAN 4031582415209



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

