

ZETA REVERSE

468STOO125P63 180°

EAN 4031582398151
Order number 00860926



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ○ ○ ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta reverse
Type	Swivel castor with spring loaded directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	700 kg
Load capacity at 6 km/h	560 kg
Load capacity Static	1400 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	164 mm
Overall weight	2.986 kg

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	55 mm
Swivel radius	117.5 mm
Swivel interference	235 mm

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ZETA REVERSE

468STOO125P63 180°

EAN 4031582398151
Order number 00860926



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

