

# LUMINA

A525PJI050S70-10X15

EAN 4031582455960



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product name                | Lumina                         |
| Housing type                | Swivel castor with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 3 km/h     | 40 kg                          |
| Load capacity Static        | 80 kg                          |
| Temperature range (Minimum) | -10 °C                         |
| Temperature range (Maximum) | 40 °C                          |
| Overall height              | 56 mm                          |
| Overall width               | 54 mm                          |
| Overall weight              | 0.056 kg                       |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Threadguards          | Without threadguard            |
| Diameter              | 50 mm                          |
| Tread width           | 10 mm                          |
| Hardness of tread (D) | 65 Shore D                     |

## HOUSING

|                     |                                       |
|---------------------|---------------------------------------|
| Material fork       | Polypropylene                         |
| Fork shape          | Twin wheel housing, closed, with dome |
| Swivel bearing      | Stem, swiveling                       |
| Swivel radius       | 62 mm                                 |
| Swivel interference | 124 mm                                |
| Thread diameter     | 10 mm                                 |

## FITTING

|              |                                      |
|--------------|--------------------------------------|
| Fitting type | Threaded stem with hexagon neck, top |
| Stem length  | 15 mm                                |

PRODUCT INFORMATION

# LUMINA

A525PJI050S70-10X15

EAN 4031582455960



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

