

# GALEA STAINLESS

5080PJM125P30-12

EAN 4031582395563



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Galea stainless           |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 100 kg                    |
| Stainless                   | ✓                         |
| Load capacity Static        | 200 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall height              | 162 mm                    |
| Overall width               | 66 mm                     |
| Overall weight              | 0.504 kg                  |

## WHEEL

|                       |                          |
|-----------------------|--------------------------|
| Body material         | Polypropylene            |
| Tread material        | Thermoplastic rubber     |
| Bearing               | Plain bearing, stainless |
| Threadguards          | With threadguard         |
| Diameter              | 125 mm                   |
| Tread width           | 30 mm                    |
| Hardness of tread (A) | 87 Shore A               |

## HOUSING

|                     |   |
|---------------------|---|
| Material fork       | Polyamide                               |
| Fork shape          | Closed                                  |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Offset              | 40 mm                                   |
| Swivel radius       | 102.5 mm                                |
| Swivel interference | 205 mm                                  |
| Dome diameter       | 59 mm                                   |

## FITTING

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 12 mm     |

# GALEA STAINLESS

5080PJM125P30-12

EAN 4031582395563



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

