

AGILA US

2670PAP3.5X1.25P30-13

EAN 4031582434620



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila US
Housing type	Swivel castor
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	113 kg
Load capacity Static	226 kg
Overall height	112.7 mm

WHEEL

Body material	Polypropylene
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	88.9 mm
Tread width	31.75 mm
Axle hole diameter	10 mm
Hardness of tread (D)	41 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Offset	34 mm
Swivel radius	78.5 mm
Swivel interference	157 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm