

KAPPA LOAD

9658FTP250P64

EAN 4031582316315
Order number 00802704



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Kappa load |
| Type | Fixed castor |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph | 4761.98 lb |
| Load capacity at 3.7 mph | 3968.32 lb |
| Load capacity Static | 9523.96 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 12.01 in |
| Overall weight | 36.77 lb |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Casting |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Threadguards | With threadguard |
| Diameter | 9.84 in |
| Tread width | 3.15 in |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|------------|----------------------------------|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Broad, reinforced |
| | ✓ |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 6.89 in |
| Plate width | 5.51 in |
| Plate hole length (Maximum) | 5.51 in |
| Plate hole width (Maximum) | 4.13 in |
| Plate hole diameter | 0.59 in |

KAPPA LOAD

9658FTP250P64

EAN 4031582316315
Order number 00802704

TECHNICAL DRAWINGS

