

# COMPACTA

1530PJO040P41

EAN 4031582425376



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product Name                | Compacta                    |
| Type                        | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 3 km/h     | 20 kg                       |
| Electric Conductive         | No                          |
| Stainless                   | No                          |
| Load capacity Static        | 40 kg                       |
| Temperature range (Minimum) | -20 °C                      |
| Temperature range (Maximum) | 60 °C                       |
| Overall Height              | 51 mm                       |
| Overall weight              | 0.07 kg                     |

## HOUSING

|                     |                                       |
|---------------------|---------------------------------------|
| Housing Material    | Steel sheet, light                    |
| Fork shape          | Twin wheel housing, closed, with dome |
| Swivel Bearing      | One ball race                         |
| Offset              | 19 mm                                 |
| Swivel radius       | 39 mm                                 |
| Swivel interference | 78 mm                                 |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread Material Mix    | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Axle                  | Riveted              |
| Threadguards          | Without threadguard  |
| Diameter              | 40 mm                |
| Tread width           | 23 mm                |
| Hardness of tread (A) | 87 Shore A           |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 37 mm        |
| Plate width                 | 37 mm        |
| Plate hole length (Maximum) | 30 mm        |
| Plate hole width (Maximum)  | 30 mm        |