

DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, super heavy
Tread material	Double flanged with tracks
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	1.02 in
Axle hole diameter	0.59 in
Hub length	1.26 in
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech plus
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	529.11 lb
Load capacity at 3.7 mph	440.92 lb
Electric conductive	no
Stainless	no
Load capacity Static	1058.22 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F

DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370

Order number 00860912
Product Drawings



BETTER MOBILITY. BETTER LIFE.

