

STYLEA

5920UJI075L51-11D20 HH 9006/9011

EAN 4031582335996



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	89 mm
Overall width	54 mm
Overall weight	0.148 kg

WHEEL

Body material	Polyamide
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	White aluminium (similar RAL9006)
Threadguards	Without threadguard
Diameter	75 mm
Tread width	8 mm
Axle hole diameter	0 mm
Hub length	0 mm
Body width	8 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Colour	White aluminium (similar RAL9006)
Offset	38 mm
Swivel radius	62 mm
Swivel interference	124 mm
Dome diameter	20 mm

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	11 mm

PRODUCT INFORMATION

STYLEA

5920UJI075L51-11D20 HH 9006/9011

EAN 4031582335996



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

