

AGILA TWIN

2977POO075P30-11

EAN 4031582452716



BETTER MOBILITY. BETTER LIFE.

CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	99 mm

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	31.4 mm
Swivel interference	198 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm